

Load Ring VRBS-FIX welded on boltable plate VRBG-FIX-50t

Artikel-Nr: 7909951




Load ring threaded with full working load in all directions and split force introduction.

- Split force introduction due to multiple point fixing.
- Suspension ring pivots 180°.
- 100% WLL at 90 degrees in the load ring plane possible.
- Clear marking of the minimum WLL for all loading directions.
- Patented markings for easy determination for withdraw of service.
- Original RUD bolt available as spare part.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Assembly with allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift. Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load Ring VRBS-FIX welded on boltable plate VRBG-FIX-50t

Artikel-Nr: 7909951



| | | |
|--------------------|-----------|------------|
| weight | 204.00 kg | 449.74 lbs |
| Nominal WLL | 50000 kg | 110230 lbs |
| T | 430 mm | 16-15/16" |
| A | 270 mm | 10-5/8" |
| B | 70 mm | 2-3/4" |
| C | 55 mm | 2-5/32" |
| D | 230 mm | 9-1/16" |
| E | 100 mm | 3-15/16" |
| F | 200 mm | 7-7/8" |
| K | 60 mm | 2-3/8" |
| L | 650 mm | 25-5/8" |
| M | M36 mm | M36 |
| N | 335 mm | 13-3/16" |