

ACP-TURNADO MAX 16t 1 3/4"-5UNC

Artikel-Nr: 7911055



The RUD ACP-TURNADO MAX sets new standards for the safe lifting of valuable loads. Thanks to its innovative, optimally protected internal spring mechanism, its lift bail immediately turns into the load direction when the load is lifted, so it cannot remain vertical. Dangerous transverse loads and a sudden drop of the load by sudden turning into the load direction are therefore impossible.


Your benefits:

- Innovative, optimally protected internal spring mechanism – prevents vertical stopping of the lift bail.
- Deflector disc with angle marking, WLL information in “t” and “lbs”, safety factors, and torque moment.
- Combination head screw with internal and external hexagon for optimised handling.
- Free space for individual marking/stamp.
- Integrated RFID transponder to make checks easier.
- Swivel joint in the lifting ring axis.
- Wear lenses for checking discard criteria.

Other important RUD specific information and specialties to our RUD lifting points can be found in the specific user instruction.

ACP-TURNADO MAX 16t 1 3/4"-5UNC

Artikel-Nr: 7911055



T	189 mm	7-7/16"
A	104 mm	4-3/32"
B	32 mm	1-1/4"
C	32 mm	1-1/4"
D	82 mm	3-1/4"
E	70 mm	2-3/4"
F	56 mm	2-3/16"
G	60 mm	2-3/8"
H	141 mm	5-9/16"
I	2-5/8" mm	2-5/8"
K	168 mm	6-5/8"
L	117 mm	4-5/8"
M	1-3/4"-5UNC mm	1-3/4"-5UNC
N	1" mm	1"
weight	7.70 kg	16.98 lbs
Nominal WLL	16000 kg	35270 lbs