

STARPOINT VRS-12t-M48

Artikel-Nr: 7984200




- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Variable bolt lengths available for tapped or through holes.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread 8UN (ANSI B1.1) - Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Tested and certified by DGUV. Testing specifications: GS-HM-36: 2023-06, Certificate No.: HM 250037
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts (Version VRS-F).
- For permanent installation and recurrent lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-12t-M48

Artikel-Nr: 7984200



weight	7.44 kg	16.40 lbs
Nominal WLL	12000 kg	26450 lbs
T	138 mm	5-7/16"
B	42 mm	1-21/32"
C	42 mm	1-21/32"
D	94 mm	3-11/16"
E	100 mm	3-15/16"
G	128 mm	5"
I	70 mm	2-3/4"
K	180 mm	7-1/16"
L	72 mm	2-27/32"
M	M48 mm	M48
N	27 mm	1-1/16"