

PowerPoint WPPH-S-1,5t

Artikel-Nr: 7989966



Weldable universal hook connection for ring assemblies, round slings, wire ropes, hook assemblies

- Can be combined with most commercial lifting means without additional connecting element.
- Large distance between bolt-on surface and load to avoid damage.
- Ideal connection link for crossbar construction.
- Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). The circular weld seam Kehlnaht 5 requires only a small welding volume.
- Compact design and high wear resistancy due to the usage of high tensile material.
- Material of weld-on-block 1.6541 (23MnNiCrMo52) (please observe user instruction).
- The WLL statement corresponds to the minimum WLL in all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Significant product characteristics of the WPP-S, WPP-B, WPP-VIP, WPPH-S, WPPH-B and WPPH-VIP are subject to property right claims.
- Component according to the test criterias of DGUV "GS-HM-36".
- Simple and fast welding installation.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint WPPH-S-1,5t

Artikel-Nr: 7989966



weight	0.90 kg	1.98 lbs
Nominal WLL	1500 kg	3300 lbs
T	141 mm	5-9/16"
A	20 mm	3/4"
B	97 mm	3-13/16"
C	25 mm	63/64"
D	40 mm	1-9/16"
G	44 mm	1-3/4"