

## PowerPoint WPPH-VIP4-0,63t

Artikel-Nr: 7989982



- Large distance between bolt-on surface and load to avoid damage.
- Ideal connection link for crossbar construction.
- Universal and non-mix-up clevis connection for easy construction with chains, hooks and eye.
- Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). The circular weld seam Kehlnaht 4 requires only a small welding volume.
- Compact design and high wear resistancy due to the usage of high tensile material. ●Material of weld-on-block 1.6541 (23MnNiCrMo52) (please observe user instruction).
- The WLL statement corresponds to the minimum WLL in all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Significant product characteristics of the WPP-S, WPP-B, WPP-VIP, WPPH-S, WPPH-B and WPPH-VIP are subject to property right claims.
- Component according to the test criterias of DGUV "GS-HM-36".
- Simple and fast welding installation.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## PowerPoint WPPH-VIP4-0,63t

Artikel-Nr: 7989982



<b>weight</b>	0.17 kg	0.37 lbs
<b>Nominal WLL</b>	630 kg	1390 lbs
<b>T</b>	34 mm	1-11/32"
<b>A</b>	4 mm	5/32"
<b>D</b>	34 mm	1-11/32"