

PowerPoint WPPH-S-0,63t

Artikel-Nr: 7990722



Weldable universal hook connection for ring assemblies, round slings, wire ropes, hook assemblies

- Can be combined with most commercial lifting means without additional connecting element.
- Large distance between bolt-on surface and load to avoid damage.
- Ideal connection link for crossbar construction.
- Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). The circular weld seam Kehlnaht 4 requires only a small welding volume.
- Compact design and high wear resistancy due to the usage of high tensile material.
- Material of weld-on-block 1.6541 (23MnNiCrMo52) (please observe user instruction).
- The WLL statement corresponds to the minimum WLL in all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Significant product characteristics of the WPP-S, WPP-B, WPP-VIP, WPPH-S, WPPH-B and WPPH-VIP are subject to property right claims.
- Component according to the test criterias of DGUV "GS-HM-36".
- Simple and fast welding installation.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint WPPH-S-0,63t

Artikel-Nr: 7990722



| | | |
|--------------------|---------|----------|
| weight | 0.30 kg | 0.66 lbs |
| Nominal WLL | 630 kg | 1390 lbs |
| T | 109 mm | 4-5/16" |
| A | 13 mm | 1/2" |
| B | 75 mm | 2-15/16" |
| C | 18 mm | 23/32" |
| D | 34 mm | 1-11/32" |
| G | 34 mm | 1-11/32" |