

Excavator hook welded VABH-W 1,5t

Artikel-Nr: 7991208




Used as a lifting point for spreader bars, wire rope slings, round slings, lifting means: oval suspension ring.

- Can be combined with most commercial lifting means without additional connecting element.
- Patented markings for easy determination for withdraw of service.
- Robust, forged safety latch.
- Phosphated surface.
- Weld-on point can be used as excavator hook.
- Simple and fast welding installation.
- Material of weld-on-block 1.6541 (23MnNiCrMo52) Weld: Kehlnaht 4 (please observe user instruction).
- Area of application in ring plane: 150°, Area of application at lateral load: +45°, -45°
- corresponds with the test criteria: "GS-HM-36"

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Excavator hook welded VABH-W 1,5t

Artikel-Nr: 7991208



| | | |
|--------------------|---------|----------|
| weight | 0.85 kg | 1.87 lbs |
| Nominal WLL | 1500 kg | 3300 lbs |
| T | 26 mm | 1" |
| A | 7,5 mm | 11/32" |
| B | 76 mm | 3" |
| C | 115 mm | 4-1/2" |
| D | 111 mm | 4-13/32" |
| E | 70 mm | 2-3/4" |
| F | 26 mm | 1" |
| I | 38 mm | 1-1/2" |