

Lashing Point Welding LPW 32000 daN without spring

Artikel-Nr: 7992229




Original VIP-Quality

- Lift bail can be pivoted through 180°.
- LC possible up to 90° in load ring plane.
- Clear indication of the lashing capacity in daN.
- Functionally optimised shape of the suspension ring for better support at side loading and protection of the clamping spring.
- Prepared for easy weld-on.
- Phosphated surface.
- Distance knobs on the weld-on block for the necessary distance for root welding.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW 32000 daN without spring

Artikel-Nr: 7992229



weight	6.80 kg	14.99 lbs
T	174 mm	6-7/8"
A	96 mm	3-25/32"
B	190 mm	7-1/2"
C	69 mm	2-23/32"
D	100 mm	3-15/16"
E	105 mm	4-1/8"
F	40 mm	1-9/16"
G	90 mm	3-17/32"
H	26 mm	1"
Lashing capacity	32000 daN	null