

Load Ring VLBS 1,5t without spring

Artikel-Nr: 7993115




Universal Lifting point for welding with a diverse operating range in engineering and plant manufacturing.

- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Suspension ring pivots 180°.
- 100 % WLL at 90° in the load ring plane possible.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Clear marking of the minimum WLL for all loading directions.
- The weld-on-block is made (forged) out of a good weldable steel. Weld: HV 5 + a 3
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2023-06, Certificate-No.: HM 240067
- Significant product characteristics of the VLBS are subject to property right claims.
- Confirmation of the deep temperature ability to -40°C by the notch bar impact test is on request possible (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load Ring VLBS 1,5t without spring

Artikel-Nr: 7993115



weight	0.35 kg	0.77 lbs
Nominal WLL	1500 kg	3300 lbs
T	65 mm	2-9/16"
A	33 mm	1-5/16"
B	66 mm	2-5/8"
C	25 mm	63/64"
D	38 mm	1-1/2"
E	40 mm	1-9/16"
F	14 mm	9/16"
G	33 mm	1-5/16"
H	14 mm	9/16"