

## Load Ring VLBS 6,7t without spring

Artikel-Nr: 7993117




Universal Lifting point for welding with a diverse operating range in engineering and plant manufacturing.

- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Suspension ring pivots 180°.
- 100 % WLL at 90° in the load ring plane possible.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Clear marking of the minimum WLL for all loading directions.
- The weld-on-block is made (forged) out of a good weldable steel. Weld: HV 12 + a 4
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2023-06, Certificate-No.: HM 240067
- Significant product characteristics of the VLBS are subject to property right claims.
- Confirmation of the deep temperature ability to -40°C by the notch bar impact test is on request possible (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## Load Ring VLBS 6,7t without spring

Artikel-Nr: 7993117



<b>weight</b>	1.89 kg	4.17 lbs
<b>Nominal WLL</b>	6700 kg	14770 lbs
<b>T</b>	117 mm	4-5/8"
<b>A</b>	61 mm	2-13/32"
<b>B</b>	115 mm	4-1/2"
<b>C</b>	44 mm	1-3/4"
<b>D</b>	67 mm	2-5/8"
<b>E</b>	73 mm	2-7/8"
<b>F</b>	24 mm	15/16"
<b>G</b>	60 mm	2-3/8"
<b>H</b>	22,5 mm	7/8"