

Lashing Point Welding LPW 3000 daN without spring

Artikel-Nr: 7993142




Original VIP-Quality

- Lift bail can be pivoted through 180°.
- LC possible up to 90° in load ring plane.
- Clear indication of the lashing capacity in daN.
- Functionally optimised shape of the suspension ring for better support at side loading and protection of the clamping spring.
- Prepared for easy weld-on.
- Phosphated surface.
- Distance knobs on the weld-on block for the necessary distance for root welding.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW 3000 daN without spring

Artikel-Nr: 7993142



weight	0.35 kg	0.77 lbs
T	65 mm	2-9/16"
A	33 mm	1-5/16"
B	66 mm	2-5/8"
C	25 mm	63/64"
D	38 mm	1-1/2"
E	40 mm	1-9/16"
F	14 mm	9/16"
G	33 mm	1-5/16"
H	14 mm	9/16"
Lashing capacity	3000 daN	null