

Lashing Point Welding LPW 8000 daN without spring

Artikel-Nr: 7993143




Original VIP-Quality

- Lift bail can be pivoted through 180°.
- LC possible up to 90° in load ring plane.
- Clear indication of the lashing capacity in daN.
- Functionally optimised shape of the suspension ring for better support at side loading and protection of the clamping spring.
- Prepared for easy weld-on.
- Phosphated surface.
- Distance knobs on the weld-on block for the necessary distance for root welding.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW 8000 daN without spring

Artikel-Nr: 7993143



weight	0.80 kg	1.76 lbs
T	83 mm	3-1/4"
A	42 mm	1-21/32"
B	87 mm	3-7/16"
C	31 mm	1-7/32"
D	51 mm	2"
E	52 mm	2-1/16"
F	18 mm	23/32"
G	46 mm	1-13/16"
H	16 mm	5/8"
Lashing capacity	8000 daN	null