

Lashing Point Welding LPW 20000 daN without spring

Artikel-Nr: 7993145




Original VIP-Quality

- Lift bail can be pivoted through 180°.
- LC possible up to 90° in load ring plane.
- Clear indication of the lashing capacity in daN.
- Functionally optimised shape of the suspension ring for better support at side loading and protection of the clamping spring.
- Prepared for easy weld-on.
- Phosphated surface.
- Distance knobs on the weld-on block for the necessary distance for root welding.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW 20000 daN without spring

Artikel-Nr: 7993145



weight	2.90 kg	6.39 lbs
T	126 mm	5"
A	75 mm	2-15/16"
B	129 mm	5-1/16"
C	55 mm	2-5/32"
D	67 mm	2-5/8"
E	71 mm	2-13/16"
F	26,5 mm	1-3/64"
G	60 mm	2-3/8"
H	26 mm	1"
Lashing capacity	20000 daN	null