

Lashing Point Welding LPW-U 5000 daN with spring

Artikel-Nr: 7994831




Original VIP-Quality

- Clear marking of the lashing capacity for all loading directions. LC marking with daN.
- Suspension ring pivots 180°.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- The weld-on-block is made (forged) out of quality weldable steel.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Phosphated surface.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW-U 5000 daN with spring

Artikel-Nr: 7994831



weight	0.48 kg	1.06 lbs
T	75 mm	2-15/16"
A	36 mm	1-27/64"
B	77 mm	3"-1/32"
C	27 mm	1-1/16"
D	45 mm	1-25/32"
E	48 mm	1-7/8"
F	16 mm	5/8"
G	40 mm	1-9/16"
H	14 mm	9/16"
Lashing capacity	5000 daN	null