

Lashing Point Welding LPW 5000 daN without spring

Artikel-Nr: 7995430




Original VIP-Quality

- Lift bail can be pivoted through 180°.
- LC possible up to 90° in load ring plane.
- Clear indication of the lashing capacity in daN.
- Functionally optimised shape of the suspension ring for better support at side loading and protection of the clamping spring.
- Prepared for easy weld-on.
- Phosphated surface.
- Distance knobs on the weld-on block for the necessary distance for root welding.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW 5000 daN without spring

Artikel-Nr: 7995430



weight	0.48 kg	1.06 lbs
T	75 mm	2-15/16"
A	36 mm	1-27/64"
B	77 mm	3"-1/32"
C	27 mm	1-1/16"
D	45 mm	1-25/32"
E	48 mm	1-7/8"
F	16 mm	5/8"
G	40 mm	1-9/16"
H	14 mm	9/16"
Lashing capacity	5000 daN	null