

## Lifting Point-Vario VWBG-V 0,45t-M10 with var. length

Artikel-Nr: 8600331



From the factory, bolt lengths from F=10-122 can be supplied ( with through thread ) When ordering implicitly indicate the required length.

- Ball bearing for a shock-free rotating and turning with less friction.
- Lifting points pivots 360°.
- Suspension ring with enlarged pivoting area.
- Comprehensive range of threads and WLL (M8 – M30 bzw. 0,3 t – 5 t).
- Available as:
  - Standard Metric Thread (DIN EN 13)
  - Metric Fine Thread (DIN EN 13)
  - Coarse Pitch Thread UNC (ANSI B1.1)
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised( compare WLL chart / product information).
- Patented markings for easy determination for withdraw of service as well as the determination of the load angle.
- Rotatable at nominal WLL, 90° to the bolt-on direction.
- Variable bolt lengths available for tapped or through holes.
- RUD bolts with special corrosion protection Corrod-DT.
- Large distance between bolt-on surface and load to avoid damage.
- Non removable special bolt (this reduces the risk of improper standard bolts).
- Component according to the test criterias of DGUV “GS-HM-36”
- Quick and easy installation with just one bolt Connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning Actions.


Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

For permanent installation of the lifting point for through hole fixtures we recommend the securing nut acc. to DIN 980-V (standard distribution, washer included), for variable installations with just one lifting action please use collar nut acc. to DIN 6331 (available upon request).

For special thread lengths in metric sizes, lock nuts (DIN 980-V crack tested) with washer are available. Collar nuts (DIN 6331, crack inspected) optionally on request.

## Lifting Point-Vario VWBG-V 0,45t-M10 with var. length

Artikel-Nr: 8600331



<b>weight</b>	0.0 kg	0.00 lbs
<b>Nominal WLL</b>	450 kg	990 lbs
<b>T</b>	78 mm	3-1/16"
<b>A</b>	8 mm	5/16"
<b>B</b>	31 mm	1-7/32"
<b>C</b>	29 mm	1-5/32"
<b>D</b>	33,5 mm	1-27/64"
<b>E</b>	30 mm	1-3/16"
<b>F</b>	10-122 mm	10-122
<b>G</b>	38 mm	1-1/2"
<b>M</b>	M10 mm	M10