

Load ring VLBG 2,5t M22 with bolt (H=33)

Artikel-Nr: 8600385




- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Exchangeable ICE-Bolt** made out of patented steel with special corrosion protection Corrud-DT. Non-hazardous deep temperature usage down to -60°; higher toughness and therefore higher bending strength as well as less wear occurrence. Original ICE-Bolt is available as a spare part. Clear marking at the bolt head: RUD, ICE, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectively flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as:
 - Standard Metric Thread (DIN EN 13)
 - Metric Fine Thread (DIN EN 13)
 - Coarse Pitch Thread UNC (ANSI B1.1)
 - Fine Thread UNF (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VLBG 2,5t M22 with bolt (H=33)

Artikel-Nr: 8600385



weight	1.31 kg	2.89 lbs
Nominal WLL	2500 kg	5500 lbs
T	110 mm	4-11/32"
A	50 mm	1-31/32"
B	82 mm	3-1/4"
C	54 mm	2-1/8"
D	45 mm	1-25/32"
E	54 mm	2-1/8"
F	16,5 mm	21/32"
G	43 mm	1-11/16"
H	33 mm	1-5/16"
I	113 mm	4-7/16"
K	64 mm	2-1/2"
L	75 mm	2-15/16"
M	M22 mm	M22
N	48 mm	1-7/8"