

Load ring VLBG 5t M30X2 with variable length

Artikel-Nr: 8600388




With a substitutable, 100% crack detected hexagon head cap bolt with thread lengths of H= 30-74 mm are available. When ordering implicitly indicate the required length.

- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Exchangeable RUD-Bolt** with special corrosion protection Corrud-DT. Original RUD-Bolt is available as a spare part. Clear marking at the bolt head: RUD, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectively flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- VLBG corresponds with the test criteria: GS-HM-36
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.
- For permanent installation of the lifting point for through hole fixtures we recommend the securing nut acc. to DIN 980-V (standard distribution, washer included), for variable installations with just one lifting action please use collar nut acc. to DIN 6331 (available upon request).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VLBG 5t M30X2 with variable length

Artikel-Nr: 8600388



Nominal WLL	5000 kg	11000 lbs
T	147 mm	5-25/32"
A	60 mm	2-3/8"
B	103 mm	4-1/16"
C	65 mm	2-9/16"
D	60 mm	2-3/8"
E	67 mm	2-5/8"
F	22,5 mm	7/8"
G	61 mm	2-13/32"
H	30-74 mm	30-74
I	151 mm	5-15/16"
K	80 mm	3-1/8"
L	91-135 mm	91-135
M	M30X2 mm	M30X2
N	67 mm	2-5/8"