

Load ring VLBG-Z 20t 2"-4,5UNC with variable length

Artikel-Nr: 8600448




Fully captive 100% crack detected hexagon head cap bolts with thread lengths of H= 51-302mm are available. When ordering implicitly indicate the required length.

- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Captive but exchangeable RUD-Bolt** with special corrosion protection Corru-DT. Original RUD-Bolt is available as a spare part. Clear marking at the bolt head: RUD, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectivley flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread UNF (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift. Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VLBG-Z 20t 2"-4,5UNC with variable length

Artikel-Nr: 8600448



Nominal WLL	20000 kg	44090 lbs
T	222 mm	8-3/4"
A	95 mm	3-3/4"
B	156 mm	6-5/32"
C	100 mm	3-15/16"
D	95 mm	3-3/4"
E	105 mm	4-1/8"
F	36 mm	1-27/64"
G	87 mm	3-7/16"
H	51-302 mm	2" up to 11-7/8"
I	230 mm	9-1/16"
K	130 mm	5-1/8"
L	138-389 mm	5-7/16" up to 15-
M	2"-4,5UNC mm	2"-4,5UNC
N	100 mm	3-15/16"