

PowerPoint PP-S-1,5t-5/8"-11UNC

Artikel-Nr: 8600582




Can be combined with most commercial lifting means without additional connecting element.

- **Double ball bearings** is the optimal solution for turning and flipping operations under full load (not suitable for permanent turning under load).
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction** Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Marking with requested torque moment and nominal WLL with a safety factor of 4:1 (MRL 2006/42/EG) and 5:1 (ASME B 30.26).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Significant product characteristics of the PP-S, PP-B and PP-VIP are subject to property right claims.
- The shape of the hook tip avoids unintentional attachment into small holes and tip loading. Robust, forged safety latch.
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint PP-S-1,5t-5/8"-11UNC

Artikel-Nr: 8600582



Nominal WLL	1500 kg	3300 lbs
T	146 mm	5-3/4"
A	20 mm	3/4"
B	97 mm	3-13/16"
C	25 mm	63/64"
D	46 mm	1-13/16"
E	41 mm	1-5/8"
F	16-24 mm	5/8" up to 15/16"
G	49 mm	1-15/16"
M	5/8"-11UNC mm	5/8"-11UNC