

PowerPoint PP-B-5t-1 1/4"-7UNC

Artikel-Nr: 8600595




- **Double ball bearing** is the optimal solution for turning and flipping operations under full load (not suitable for permanent turning under load).
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction** Lowest kinking possibility due to cardan joint.
- **Suspension ring with enlarged pivoting area.**
- Clear marking of the minimum WLL for all loading directions.
- Marking with requested torque moment and nominal WLL with a safety factor of 4:1 (MRL 2006/42/EG) and 5:1 (ASME B 30.26).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Significant product characteristics of the PP-S, PP-B and PP-VIP are subject to property right claims. ● Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint PP-B-5t-1 1/4"-7UNC

Artikel-Nr: 8600595



weight	5.20 kg	11.46 lbs
Nominal WLL	5000 kg	11000 lbs
T	223 mm	8-25/32"
A	21 mm	13/16"
B	130 mm	5-1/8"
C	60 mm	2-3/8"
D	95 mm	3-3/4"
E	85 mm	3-11/32"
F	45 mm	1-25/32"
G	93 mm	3-21/32"
M	1 1/4"-7UNC mm	1 1/4"-7UNC
N	25 mm	63/64"