

## ACP-TURNADO 2,5t M16 with variable length

Artikel-Nr: 8600634



Fully captive 100% crack detected hexagon head cap bolts with thread lengths of F= 16-149 mm are available. **When ordering implicitly indicate the required length.** Including washers and crack detected nuts.

The RUD ACP-TURNADO, with its unique spring mechanism, ensures greater safety by automatically rotating in the direction of force transmission and by actively preventing a hazardous stop-page of the ring.

The RUD ACP-TURNADO reacts actively and avoids self-contained the „worst-case-scenario“-area with this high transverse loading. Its ingenious spring mechanism turns the lift ring automatically into the direction of an optimal force transmission. No tilting. No unintentional reverting.

This revolutionary design, in combination with the especially for RUD developed ICE fine grain steel bolt technology sets the new standard. The result? Up to 30% higher WLL compared to matchable design sizes.


Your benefits:

- Innovative exterior spring mechanism – prevents vertical stopping of the bracket.
- Round lift bail – no clinking possible.
- Combination head threaded rod with internal and external hexagon for optimised handling; up to M24 (1”) as RUD ICE-BOLT.
- Integrated RFID transponder to make checks easier.
- Swivel joint in the lifting ring axis.
- Wear lenses for checking discard criteria.

Other important RUD specific information and specialties to our RUD lifting points can be found in the specific user instruction.

## ACP-TURNADO 2,5t M16 with variable length

Artikel-Nr: 8600634



Nominal WLL	2500 kg	4400 lbs
<b>T</b>	107 mm	4-7/32"
<b>B</b>	14 mm	9/16"
<b>C</b>	14 mm	9/16"
<b>D</b>	50 mm	1-31/32"
<b>E</b>	40 mm	1-9/16"
<b>F</b>	16-149 mm	5/8" up to 5-7/8"
<b>G</b>	36 mm	1-27/64"
<b>H</b>	68-195 mm	2-11/16" up to 7-
<b>I</b>	24 mm	15/16"
<b>K</b>	76 mm	3"
<b>L</b>	52-185 mm	2-1/16" up to 7-
<b>M</b>	M16 mm	M16
<b>N</b>	10 mm	3/8"