



Product availability: Stock - Normally stocked in distribution facility



### Main

Range	TeSys
Device short name	GVAD
Product or component type	Auxiliary contact block
Product compatibility	GV3L GV2P GV2LE GV2RT GV2L GV2ME GV3P
Mounting location	Left side
Auxiliary contacts operation	Fault signal 1 NC
Pole contact composition	2 NC
Connections - terminals	Screw clamp terminals 1 0.00...0.00 in <sup>2</sup> (1... 2.5 mm <sup>2</sup> )solid Screw clamp terminals 2 0.00...0.00 in <sup>2</sup> (1... 2.5 mm <sup>2</sup> )solid Screw clamp terminals 1 0.00...0.00 in <sup>2</sup> (0.75... 2.5 mm <sup>2</sup> )flexible without cable end Screw clamp terminals 2 0.00...0.00 in <sup>2</sup> (0.75... 2.5 mm <sup>2</sup> )flexible without cable end Screw clamp terminals 2 0.00...0.00 in <sup>2</sup> (0.75... 1.5 mm <sup>2</sup> )flexible with cable end Screw clamp terminals 1 0.00...0.00 in <sup>2</sup> (0.75... 1.5 mm <sup>2</sup> )flexible with cable end

### Complementary

[Ui] rated insulation voltage	690 V IEC 60947-1 300 V UL 508 300 V CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A 2.5 A fault signalling
Protection type	GB2CB... circuit breaker rating according to operational current for Ue ≤ 415 V GG fuse 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	300 VA 48 V AC-15 100000 cycles 414 VA 690 V AC-15 100000 cycles 500 VA 110...127 V AC-15 100000 cycles 500 VA 500 V AC-15 100000 cycles 650 VA 440 V AC-15 100000 cycles 720 VA 230...240 V AC-15 100000 cycles 850 VA 380...415 V AC-15 100000 cycles 36 VA 24 V AC-14 1000 cycles 48 VA 48 V AC-14 1000 cycles 72 VA 110...127 V AC-14 1000 cycles

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Rated operational power in W	120 W 240 V DC-13 100000 cycles 140 W 110 V DC-13 100000 cycles 140 W 24 V DC-13 100000 cycles 180 W 60 V DC-13 100000 cycles 240 W 48 V DC-13 100000 cycles 15 W 48 V DC-13 1000 cycles 24 W 24 V DC-13 1000 cycles 9 W 60 V DC-13 1000 cycles
Tightening torque	12.39 lbf.in (1.4 N.m) screw clamp terminals
Height	3.50 in (89 mm)
Width	0.37 in (9.3 mm)
Depth	2.60 in (66 mm)
Product weight	0.12 lb(US) (0.055 kg)

## Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

## Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901212386
Package weight(Lbs)	0.05 kg (0.11 lb(US))
Returnability	Yes
Country of origin	CZ

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

---

---

GVAD0101

