



Main

| | |
|---------------------------|--|
| Range of Product | TeSys D |
| Range | TeSys Linergy |
| Device short name | LAD9 |
| Product or Component Type | Set of connections |
| Poles description | 3P |
| Electrical circuit type | Reversing contactor |
| Range compatibility | TeSys D |
| Product Compatibility | LC1D09 LC1D12 LC1D18 LC1D25 LC1D32 LC1D38 |

Complementary

| | |
|-------------------------|-----------------------|
| Mounting Location | Downstream |
| Connections - terminals | Screw clamp terminals |

Ordering and shipping details

| | |
|-----------------------|--------------------------------------|
| Category | 22354 - CTR, TESYS D, OPEN, 9-38A AC |
| Discount Schedule | I12 |
| GTIN | 3389110223668 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.95 oz (27 g) |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.79 in (2 cm) |
| Package 1 width | 1.97 in (5 cm) |
| Package 1 Length | 3.86 in (9.8 cm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 10.37 oz (294 g) |
| Package 2 Height | 3.86 in (9.8 cm) |
| Package 2 width | 3.86 in (9.8 cm) |
| Package 2 Length | 5.91 in (15 cm) |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 140 |
| Package 3 Weight | 10.14 lb(US) (4.6 kg) |
| Package 3 Height | 11.81 in (30 cm) |
| Package 3 width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|