





Main

| | |
|---|---|
| Range | TeSys |
| Product name | TeSys D |
| Product or component type | Contacteur |
| Device short name | LC1D |
| Contacteur application | Resistive load Motor control |
| Utilisation category | AC-1 AC-3 AC-4 |
| Poles description | 3P |
| Power pole contact composition | 3 NO |
| [Ue] rated operational voltage | Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC |
| [Ie] rated operational current | 60 A 140 °F (60 °C) <= 440 V AC AC-1 power circuit 40 A 140 °F (60 °C) <= 440 V AC AC-3 power circuit |
| Motor power kW | 18.5 kW 380...400 V AC 50/60 Hz AC-3) 11 kW 220...230 V AC 50/60 Hz AC-3) 22 kW 415...440 V AC 50/60 Hz AC-3) 22 kW 500 V AC 50/60 Hz AC-3) 30 kW 660...690 V AC 50/60 Hz AC-3) 9 kW 400 V AC 50/60 Hz AC-4) |
| Motor power HP (UL / CSA) | 5 Hp 230/240 V AC 50/60 Hz 1 phase 10 Hp 230/240 V AC 50/60 Hz 3 phase 30 Hp 575/600 V AC 50/60 Hz 3 phase 10 Hp 200/208 V AC 50/60 Hz 3 phase 3 Hp 115 V AC 50/60 Hz 1 phase 30 hp 460/480 V AC 50/60 Hz 3 phase |
| Control circuit type | AC 50/60 Hz |
| [Uc] control circuit voltage | 110 V AC 50/60 Hz |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 6 kV IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 10 A 140 °F (60 °C) signalling circuit 60 A 140 °F (60 °C) power circuit |
| Irms rated making capacity | 140 A AC signalling circuit IEC 60947-5-1 250 A DC signalling circuit IEC 60947-5-1 800 A 440 V power circuit IEC 60947 |
| Rated breaking capacity | 800 A 440 V power circuit IEC 60947 |
| [Icw] rated short-time withstand current | 320 A 104 °F (40 °C) - 10 s power circuit 720 A 104 °F (40 °C) - 1 s power circuit 72 A 104 °F (40 °C) - 10 min power circuit 165 A 104 °F (40 °C) - 1 min power circuit 100 A - 1 s signalling circuit 120 A - 500 ms signalling circuit 140 A - 100 ms signalling circuit |
| Associated fuse rating | 10 A gG signalling circuit IEC 60947-5-1 80 A gG <= 690 V type 1 power circuit 80 A gG <= 690 V type 2 power circuit |
| Average impedance | 1.5 mOhm - Ith 60 A 50 Hz power circuit |
| [Ui] rated insulation voltage | Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL Power circuit 690 V IEC 60947-4-1 |
| Electrical durability | 1.4 Mcycles 60 A AC-1 <= 440 V 1.5 Mcycles 40 A AC-3 <= 440 V |
| Power dissipation per pole | 2.4 W AC-3 5.4 W AC-1 |

| | |
|--------------------------|--|
| Safety cover | With |
| Mounting support | Rail Plate |
| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 |
| Product certifications | CCC CSA GOST UL |
| Connections - terminals | Control circuit screw clamp terminals 2 0.00... 0.00 in ² (1...2.5 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)solid without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²)solid without cable end Power circuit screw connection 1 0.00...0.05 in ² (1... 35 mm ²)flexible without cable end Power circuit screw connection 2 0.00...0.04 in ² (1... 25 mm ²)flexible without cable end Power circuit screw connection 1 0.00...0.05 in ² (1... 35 mm ²)flexible with cable end Power circuit screw connection 2 0.00...0.04 in ² (1... 25 mm ²)flexible with cable end Power circuit screw connection 1 0.00...0.05 in ² (1... 35 mm ²)solid without cable end Power circuit screw connection 2 0.00...0.04 in ² (1... 25 mm ²)solid without cable end |
| Tightening torque | Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Power circuit 70.81 lbf.in (8 N.m) EverLink BTR screw connectors 0.04...0.05 in ² (25...35 mm ²) hexagonal 0.16 in (4 mm) Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors 0.00...0.04 in ² (1...25 mm ²) hexag- onal 0.16 in (4 mm) |
| Operating time | 4...19 ms opening 12...26 ms closing |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 2000000 cycles contactor with mechanical load EN/ISO 13849-1 |
| Mechanical durability | 6 Mcycles |
| Maximum operating rate | 3600 cyc/h 140 °F (60 °C) |

Complementary

| | |
|---------------------------------|--|
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | Drop-out 0.3...0.6 Uc AC 50/60 Hz 140 °F (60 °C)) Operational 0.8...1.1 Uc AC 50 Hz 140 °F (60 °C)) Operational 0.85...1.1 Uc AC 60 Hz 140 °F (60 °C)) |
| Inrush power in VA | 140 VA 60 Hz 0.75 68 °F (20 °C)) 160 VA 50 Hz 0.75 68 °F (20 °C)) |
| Hold-in power consumption in VA | 13 VA 60 Hz 0.3 68 °F (20 °C)) 15 VA 50 Hz 0.3 68 °F (20 °C)) |
| Heat dissipation | 4...5 W 50/60 Hz |
| Auxiliary contacts type | Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA signalling circuit |
| Minimum switching voltage | 17 V signalling circuit |

| | |
|-----------------------|---|
| Non-overlap time | 1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact |
| Insulation resistance | > 10 MOhm signalling circuit |

Environment

| | |
|---|--|
| IP degree of protection | IP20 front face IEC 60529 |
| Protective treatment | TH IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | 23...140 °F (-5...60 °C) |
| Ambient air temperature for storage | -76...176 °F (-60...80 °C) |
| Permissible ambient air temperature around the device | -40...158 °F (-40...70 °C) at Uc |
| Operating altitude | 9842.52 ft (3000 m) without |
| Fire resistance | 1562 °F (850 °C) IEC 60695-2-1 |
| Flame retardance | V1 UL 94 |
| Mechanical robustness | Vibrations contactor open2 Gn, 5...300 Hz Vibrations contactor closed4 Gn, 5...300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open10 Gn for 11 ms |
| Height | 4.80 in (122 mm) |
| Width | 2.17 in (55 mm) |
| Depth | 4.72 in (120 mm) |
| Net weight | 1.87 lb(US) (0.85 kg) |

Ordering and shipping details

| | |
|---------------------|---------------------------------------|
| Category | 22357 - CTR, TESYS D, OPEN, 40-65A AC |
| Discount Schedule | I12 |
| GTIN | 00785901728740 |
| Package weight(Lbs) | 0.94 kg (2.08 lb(US)) |
| Returnability | Yes |
| Country of origin | ID |


Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



(1) Minimum electrical clearance

| LC1 | | D40A...D65A |
|-----|------------------------------------|-------------|
| a | | 55 |
| b1 | with LA4 D•2 | – |
| | with LA4 DB3 or LAD 4BB3 | 136 |
| | with LA4 DF, DT | 157 |
| | with LA4 DM, DW, DL | 166 |
| c | without cover or add-on blocks | 118 |
| | with cover, without add-on blocks | 120 |
| c1 | with LAD N (1 contact) | – |
| | with LAD N or C (2 or 4 contacts) | 150 |
| c2 | with LA6 DK10, LAD 6DK | 163 |
| c3 | with LAD T, R, S | 171 |
| | with LAD T, R, S and sealing cover | 175 |

Wiring

