

MICO electronic circuit protection, 4 CHANNELS

IN: 24 V DC OUT: 24 V DC / 2x 1-2-3-4 A & 2x 4-6-8-10 A


MICO 4.4.10 ACTUATOR-SENSOR

4 channels

Current adjustment 2x 1 A, 2 A, 3 A, 4 A; 2x 4 A, 6 A, 8 A, 10 A

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Input**

Operating voltage 24 V DC (18...30 V DC)

Output

Current adjustment 1 A, 2 A, 3 A, 4 A; 4 A, 6 A, 8 A, 10 A, by countersunk rotary switch, sealed

Inrush capacity max. 20 mF (per channel)

Control inputs

Input voltage (ON) 10...30 V DC

Impulse length (ON) min. 20 ms

Control outputs

Group alarm output potential free 30 V AC/DC, 100 mA

General data

Connection Spring clamp terminals

Input terminals 2x 16 mm²Output terminals per output 1x 4 mm²Alarm terminals 2.5 mm²

Bridging concept two sides, with spring clamp terminals or bridge set (max. 40 A)

Mounting method DIN-rail mountable TH35 (EN 60715)



Dimensions HxWxD 90x70x80 mm

Temperature range 0...+55 °C (storage temperature -40...+80 °C)

Commercial data

country of origin	CZ
customs tariff number	85363010
EAN	4048879294515
eClass	27141901
Packaging unit	1

Sketch



Product may differ from Image