

**MICO BASIC 4.2 electronic circuit protection, 4 CHANNELS**

IN: 24 V DC OUT: 24 V / 2 A

MICO BASIC 4.2  
4 channels  
Current adjustment 2 A

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals****Input**

Operating voltage	24 V DC (18...30 V DC)
-------------------	------------------------

**Output**

Current adjustment	2 A
Inrush capacity	max. 20 mF (per channel)

**Control inputs**

Input voltage (ON)	10...30 V DC
Impulse length (ON)	min. 20 ms

**Control outputs**

Group alarm output	max. 20 mA; high: all channels ON; low: not all channels ON
--------------------	---

**General data**



Connection	Spring clamp terminals
Input terminals	1 × 16 mm <sup>2</sup>
Output terminals	per output 1 × 4 mm <sup>2</sup>
Alarm terminals	2.5 mm <sup>2</sup>
Bridging concept	one side, with spring clamp terminals or bridge set (max. 40 A)
Mounting method	DIN-rail mountable TH35 (EN 60715)
Dimensions H×W×D	90×36×80 mm

Temperature range 0...+55 °C (storage temperature -40...+80 °C)

#### Commercial data

country of origin	CZ
customs tariff number	85363010
EAN	4048879327145
eClass	27141901
Packaging unit	1

#### Sketch



Product may differ from Image