

MICO BASIC 4.6 electronic circuit protection, 4 CHANNELS

IN: 24 V DC OUT: 24 V DC / 6 A

MICO BASIC 4.6

4 channels

Current adjustment 6 A

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Input**

Operating voltage 24 V DC (18...30 V DC)

Output

Current adjustment 6 A

Inrush capacity max. 20 mF (per channel)

Control inputs

Input voltage (ON) 10...30 V DC

Impulse length (ON) min. 20 ms

Control outputs

Group alarm output max. 20 mA; high: all channels ON; low: not all channels ON

General data

Connection Spring clamp terminals

Input terminals 1 × 16 mm²Output terminals per output 1 × 4 mm²Alarm terminals 2.5 mm²

Bridging concept one side, with spring clamp terminals or bridge set (max. 40 A)

Mounting method DIN-rail mountable TH35 (EN 60715)

Dimensions H×W×D 90×36×80 mm

