



Product Benefits

Brighter Lines – The fully adjustable pump allows you to apply the perfect amount of pressure to produce a high quality line without wasting paint.

Easy To Use – The airless pump pulls the paint directly from any standard 5-gallon pail. A universal lid snaps on any pail to prevent spills.

Easy Cleanup – Color changes and clean up can be done in less than 5 minutes. Simply remove the pail with unused striping paint, place a half filled pail of water or solvent (depending on the paint) on the machine and flush the system. Run the liquid pump protector through the system, and you are ready for the next striping job.

Product Overview

The Newstripe 4400™ Airless Striping Machine will out perform other paint striping machines costing hundreds more. The fully adjustable pressure pump lets you spray without wasting paint. Easy to use, handle mounted controls let you quickly and efficiently stripe without time consuming and costly set up.

Fast and Simple to Use

1. Works on Athletic fields and Pavement
2. The hydraulic driven pump is non-pulsating so you get the best line edges possible.
3. Dual handles with cushioned grips and all welded steel construction
4. It's unique, simple design is easy and inexpensive to maintain.
5. Quickly change your paint colors.

Specifications

Item Name	4400™ Airless Striping Machine
Item Number	10003566 10004831 optional cleaning tank
Application	Athletic Fields and Pavement
Power Source	Engine, 127cc Briggs & Stratton, OHV with oil alert
Pump Detail	Newstripe- Airless, .44gpm, adjustable 0-3000 psi
Paint Capacity	5 gallon pail
Dimensions	44" H x 58" W x 25" L
Warranty	36 Months (Engine and spray pump 12 months)
Shipping weight	170 lbs.
Includes	Airless, spray gun with reversible tip. 2"-6 adjustable line width, 25' hose, 5 gallon pail. Four, 10" pneumatic tires

Premium Performance, Economical Price

With the 4400™ Airless Stripping Machine

**Product Features**

Brighter Lines: The fully adjustable, 0-3000 psi airless pump lets you control the perfect pressure for all paint, thinned or non-thinned. The result is a higher quality line without wasting paint. Plus, the hydraulic driven, non-pulsating pump give you the best line edges possible. Eliminate ragged and scalloped edges common with pulsating piston pumps.



Versatile: A quick release clamp allows you to remove the spray gun to paint stencils, curbs, and hard to reach areas with a 25 foot length hose. An optional HashMark™ Master II is also available to easily and quickly create hash marks on athletic fields.



Smooth and Economical: The 127 cc Briggs and Stratton engine features an OHV design for fuel economy and smooth operation. Plus, the included oil alert won't let you damage the engine from low oil. Four 10" pneumatic tires make for easy rolling.



Easy Clean Up: The optional 1 gallon optional cleaning tank lets you clean your spray gun and hoses without leaving the field . Quickly and easily attaches to the right side of the machine.