




# 4' x Custom Length, Charcoal, Evergreen Diamond™ Debris Capture Entrance Mat, 125

## Product Images



## Short Description

---

- Nylon carpet fibers made from 100% recycled material
- Tufted loop pile construction for dying and cleaning
- 25 ounce tufted loop pile yarn per square yard
- Low profile to perform in narrow clearance doorways
- Vinyl backing ensures minimal buckling and mat movement

## Description

---

Evergreen Diamond™ features a fashionable diamond pattern design made from 100% recycled carpet fibers. A hefty 25 ounce per square yard tufted loop-pile top surface allows the mat to capture debris and moisture while maintaining its attractive appearance. A heavy-weight vinyl non-slip backing ensures minimum movement. Evergreen Diamond™ is perfect for use at indoor main entranceways or any and all medium to heavy traffic areas.

# Specifications

|                            |                                                                                                           |
|----------------------------|-----------------------------------------------------------------------------------------------------------|
| Model No                   | 125C0048CH                                                                                                |
| Color                      | Charcoal                                                                                                  |
| Dimensions                 | 4ft x Specify Length                                                                                      |
| Thickness                  | 3/8in                                                                                                     |
| UPC                        | 662641839564                                                                                              |
| Brand                      | NoTrax                                                                                                    |
| Custom Lengths             | 3', 4' and 6' widths (up to 60' long)                                                                     |
| Group                      | Entrance Matting                                                                                          |
| Environment                | Indoor                                                                                                    |
| Recommended Use            | For placement inside entrances of offices, shops, restaurants, grocery shops, bakeries, specialty stores. |
| Special Remarks            | Use for indoor main entry ways while maintaining an attractive appearance                                 |
| Edges                      | Vinyl borders                                                                                             |
| Usage Intensity            | Medium traffic                                                                                            |
| Material Specifications    | Nylon                                                                                                     |
| Surface Detail             | Rich Monochrome Colors                                                                                    |
| Backing                    | Black vinyl (DOP free)                                                                                    |
| Process                    | Tufting                                                                                                   |
| Pile Weight Oz             | 25                                                                                                        |
| Weight Lbs/sqft            | 0.63                                                                                                      |
| Thickness Inch             | 3/8in                                                                                                     |
| Fire Rating US             | Pass                                                                                                      |
| Dust Control Rating        | Best                                                                                                      |
| Water Retention Rating     | Best                                                                                                      |
| Crush Resistance Rating    | Best                                                                                                      |
| Function Appearance Rating | Superior                                                                                                  |