



### Main

Range	Multi 9
Product name	Multi 9 C60
Product or Component Type	Miniature circuit-breaker
Device short name	C60SP
Device Application	Distribution
Poles description	2P
Number of protected poles	2
Line Rated Current	1 A 77 °F (25 °C) EN/IEC 60947-2
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	14 KA AIR 240 V AC UL 1077 14 KA AIR 240 V AC CSA C22.2 No 235 10 KA AIR 480Y/277 V AC UL 1077 10 KA AIR 125 V DC UL 1077 10 KA AIR 480Y/277 V AC CSA C22.2 No 235 10 KA AIR 125 V DC CSA C22.2 No 235 6 KA Icu 440 V AC EN/IEC 60947-2 10 KA Icu 415 V AC EN/IEC 60947-2 20 KA Icu 240 V AC EN/IEC 60947-2 6 KA Icu 440 V AC GB 14048.2 10 KA Icu 415 V AC GB 14048.2 20 KA Icu 240 V AC GB 14048.2
Suitability for isolation	Yes EN/IEC 60947-2
Standards	EN/IEC 60947-2 GB 14048.2 UL 1077 CSA C22.2 No 235
Product certifications	IEC CCC UR CSA

### Complementary

[Ue] rated operational voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 440 V AC 50/60 Hz
Magnetic tripping limit	8.5 x In +/- 20 % AC 12 x In +/- 20 % DC
[Ics] rated service breaking capacity	4.5 KA 75 % EN/IEC 60947-2 - 440 V AC 7.5 KA 75 % EN/IEC 60947-2 - 415 V AC 15 KA 75 % EN/IEC 60947-2 - 240 V AC 4.5 KA 75 % GB 14048.2 - 440 V AC 7.5 KA 75 % GB 14048.2 - 415 V AC 15 KA 75 % GB 14048.2 - 240 V AC
[Ui] rated insulation voltage	500 V AC EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kVEN/IEC 60947-2
Contact position indicator	Yes
Control Type	Toggle
Local signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail

9 mm pitches	4
Height	3.19 in (81 mm)
Width	1.42 in (36 mm)
Depth	2.83 in (72 mm)
Color	Gray
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Tunnel type terminal top or bottom) 0.00...0.04 in <sup>2</sup> (1...25 mm <sup>2</sup> ) AWG 18...AWG 8) - rigid Tunnel type terminal top or bottom) 0.00...0.02 in <sup>2</sup> (1...16 mm <sup>2</sup> ) AWG 18...AWG 8) - flexible with ferrule Tunnel type terminal top or bottom) 0.00...0.02 in <sup>2</sup> (1...16 mm <sup>2</sup> ) AWG 18...AWG 8) - flexible
Wire stripping length	0.55 in (14 mm) top or bottom
Tightening torque	22.13 lbf.in (2.5 N.m) top or bottom
Earth-leakage protection	Without

## Environment

IP degree of protection	IP20(IEC 60529 IP40 modular enclosure)IEC 60529
Pollution degree	3 EN/IEC 60947-2
Tropicalisation	2 IEC 60068-1
Relative humidity	95 % 131 °F (55 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

## Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	3606481168450
Nbr. of units in pkg.	1
Package weight(Lbs)	8.25 oz (234 g)
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.42 in (3.6 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	3.35 in (8.5 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Weight	3.20 lb(US) (1.451 kg)
Package 2 Height	3.54 in (9 cm)
Package 2 width	3.15 in (8 cm)
Package 2 Length	9.06 in (23 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Weight	39.46 lb(US) (17.899 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product