



### Main

Range	PowerLogic
Range of product	PowerLogic EM3500
Device short name	EM3502
Product or Component Type	Energy meter
Metering type	Demand power P, Q, S Peak demand power PM, QM, SM Current I1, I2, I3, Iavg Voltage U21, U32, U13, V1, V2, V3

### Complementary

Poles description	3P + N
Type of measurement	Active and reactive power total Active and reactive power per phase Apparent power total Apparent power per phase Power factor total Power factor per phase Peak demand power Current Voltage Frequency
Device Application	Partial meter Sub billing
Accuracy class	Class 0.2S power IEC 62053-22 Class 0.2S energy IEC 62053-22 Class 0.2S power ANSI C12.20 Class 0.2S energy ANSI C12.20
Measurement accuracy	Power +/- 0.2 % Energy +/- 0.2 %
Input type	Split core current transducer 0.333 V or 1 V
Rated voltage	90...347 V
Network Frequency	60 Hz 50 Hz
Technology Type	Electronic
Display Type	Backlit LCD
Measurement current	5...32000 A
Display digits	5
Information displayed	Status and alert Communication with system Input/Output status Error Tx activity Rx activity Instant power per usage
Tamperproof of settings	Protected by access code
Communication port protocol	-
Communication Service	Total cumulated active energy Total cumulated energy
Data recording	Energy consumption logs
Demand intervals	Fixed or rolling block
Local signalling	Red LED threshold reached Green flashing LED output signal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Number of Outputs	2 pulse 1 alarm output
Output voltage	30 V AC/DC
[Ue] rated operational voltage	90...347 V AC 50/60 Hz between phase and neutral UL 156...600 V AC 50/60 Hz between phases UL 90...300 V AC 50/60 Hz between phase and neutral CE 125...300 V DC
Power consumption in VA	5 VA 347 V AC between phase and neutral) 5 VA 600 V AC between phases)
Power consumption in W	3 W 300 V
Ride-through time	100 ms 120 V AC
Mounting Mode	Clip-on By screws
Mounting Support	DIN rail
Standards	UL 508 CSA C22.2 No 14-05 IEC 61010-1
Product certifications	CE IEC 61010 CULus UL 508

## Environment

Relative humidity	0...95 %
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Color	Dark grey
9 mm pitches	12
Width	4.21 in (107 mm)
Height	3.58 in (91 mm)
Depth	2.32 in (59 mm)





## Ordering and shipping details

Category	09798 - POWERLOGIC EM3500 SERIES
Discount Schedule	PL1
GTIN	3606481969255
Nbr. of units in pkg.	1
Package weight(Lbs)	8.00 lb(US) (3.629 kg)
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.58 in (9.1 cm)
Package 1 width	4.21 in (10.7 cm)
Package 1 Length	2.32 in (5.9 cm)

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.