







Fire Retardant Mat Niru® Cushion-Ease® 650SFR

Product Images





Short Description

- Resilient rubber compound and unique multi-nib support design offers exceptional fatigue relief
- Large hole drainage design keeps moisture and debris free away
- Easy to snap-together system for on-site custom work station platforms
- Nitrile provides highest level of resistance to chemicals, oils and greases
- Fire Retardant meets the Federal Flammability Standard DOC FF 1-70. The mat is chemically treated to be slow burning or self-extinguishing when exposed to an open flame. Meets NFPA Safety Code 101 Class 1.
- Compatible with any Cushion-Ease® family mats
- 551 M.D. Ramp System® and 552 extra wide M.D.-X Ramp System™ available

Description

Niru® Cushion-Ease® FR is a high performance interlocking anti-fatigue fire resistant mat system made with a resilient rubber compound with a drainage top anti-slip surface texture and a multi-nib backing for comfort and ergonomic support of the mat. Made of 100% nitrile rubber compound that provides the highest resistance to chemicals, cutting fluids, animal fats, oils and greases. Fire Retardant rubber is chemically treated to be slow burning or self-extinguishing when exposed to an open flame. Niru® Cushion-Ease® FR mold has been engineered to produce a mat that is functional, comfortable and durable. Large holes provide excellent drainage and aeration leaving a dry, clean work area. All Cushion-Ease® series mats have a male/female interlocking system for individual workstations, long runs, unique configurations and wall-to-wall floors. Also compatible with NoTrax® M.D. Ramp System® for easy on-site custom configurations and trip-resistant platforms.

Specifications

Model No	650SFR
Available Colors	Black
Overall Thickness	3/4
Standard sizes	3'x 3'; 3'x 5'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Oily Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, production lines, assembly lines, CNC machines, metal working for individual workstations and custom work platforms
Special Remarks	Easy to make custom configurations on-site by utilizing the 551 M.D. Ramp System® and 552 extra wide M.D.-X Ramp System™
Surface	Structured Pebble Pattern
Edges	Attachable beveled edges are available
Usage Intensity	Heavy duty
Custom Description	Available #551 M.D. Ramp System® or #552 M.D.-X Ramp System™ attachable ramps
Installation	Interlocking mats allow on-site customization. Square snap-together units can be assembled effortlessly.
Material Specifications	100% nitrile fire retardant rubber compound
Process	Compression Molding
Weight Lbs/sqft	2.8
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best
Slip Resistance Rating	Best
Wear Resistance Rating	Best

Prop 65

⚠️WARNING: This product can expose you to chemicals including diisodecyl phthalate which is known to the State of California to cause birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.

Product Options

Dimensions:	3ft x 3ft
	3ft x 5ft