

3' x 5', Black, Niru® Cushion-Ease® GSII™ Interlocking Rubber Mat, 850

Product Images



Short Description

- Resilient rubber compound and unique multi-nib support design offers exceptional fatigue relief
- Large hole drainage design keeps moisture and debris free away
- Easy to snap-together system for on-site custom work station platforms
- Nitrile provides highest level of resistance to chemicals, oils and greases
- GSII™ offers the ultimate in durability, performance and traction in harsh environments

Description

Niru® Cushion-Ease® GSII™ is a high performance interlocking anti-fatigue matting system made with a resilient rubber compound with a drainage top anti-slip surface texture and a multi-nib backing for comfort and ergonomic support of the mat. Made of 100% nitrile rubber compound that provides the highest resistance to chemicals, cutting fluids, animal fats, oils and greases. GSII™ has a silicon carbide grit surface for extreme traction in the harshest of work environments. Niru® Cushion-Ease® GSII™ mold has been engineered to produce a mat that is functional, comfortable and durable. Large holes provide excellent drainage and aeration leaving a dry, clean work area. All Cushion-Ease® series mats have a male/female interlocking system for individual workstations, long runs, unique configurations and wall-to-wall floors. Also compatible with NoTrax® M.D. Ramp System® for easy on-site custom configurations and trip-resistant platforms.

Specifications

Model No	850S0035BL
Color	Black
Dimensions	3ft x 5ft
Thickness	3/4in
UPC	662641768116
Brand	NoTrax
Available Colors	Black
Standard sizes	3'x3', 3'x5'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Oily Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, production lines, assembly lines, CNC machines, metal working for individual workstations and custom work platforms
Special Remarks	GSII™ excels in the harshest industrial environments because it resists the chemicals, oils, and greases that cause traditional rubber matting to breakdown
Edges	Attachable beveled edges are available
Usage Intensity	Heavy duty
Custom Description	Available #551 M.D. Ramp System® or #552 M.D.-X Ramp System™ attachable ramps
Installation	Interlocking mats allow on-site customization. Square snap-together units can be assembled effortlessly.
Material Specifications	100% Nitrile rubber
Surface Detail	Grip Step II®
Process	Compression Molding
Pallet Quantity	36
Weight Lbs/sqft	2.9

Thickness Inch	3/4in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best
Slip Resistance Rating	Superior
Wear Resistance Rating	Superior

Prop 65

⚠️WARNING:This product can expose you to chemicals including diisodecyl phthalate which is known to the State of California to cause birth defects or reproductive harm, and 2-mercaptobenzothiazole and beryllium which are known to the State of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.