
3' x 12', Black, Pebble Trax® Grande™ Anti Fatigue Mat, 980

Product Images



Short Description

- The pebble embossed rubber top surface is combined with a dense closed cell PVC foam base
- Spark resistant
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage
- Beveled edges on all 4 sides

Description

Pebble Trax® Grande™ is a full ONE-INCH thick anti-fatigue floor mat providing the ultimate in comfort and ergonomic support in dry environments such as assembly lines, lab areas, machine workstations and packaging areas. The pebble-embossed rubber top provides non-directional traction and is easy to clean and resists exposure to sparks from welding. Made with a resilient SBR rubber compound, the top surface is combined with a dense closed cell foam base utilizing Notrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. All Notrax® laminate floor mats come standard with RedStop™, a uniquely engineered non-slip backing technology that eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Specifications

Model No	980S0312BL
Color	Black
Dimensions	3ft x 12ft
Thickness	1in
UPC	662641750999
Brand	NoTrax
Roll Sizes	2'x75', 3'x75', 4'x75'
Custom Lengths	2', 3' and 4' widths (up to 75' long)
Standard sizes	2'x3', 3'x5', 3'x12'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Easy to clean non-directional top surface
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	Rubber on microcellular vinyl base
Surface Detail	Structured Pebble Pattern
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	2
Thickness Inch	1in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).

Anti-Fatigue Rating	Superior
Slip Resistance Rating	Superior
Wear Resistance Rating	Superior