

2' x 3', Red, Multi Mat™ II Drainage Anti Slip Mat, T23RD

Product Images



Short Description

- Non-skid surface for added traction
- Reversible for extended life
- Low profile for easy cart access
- Nitrile Grease Resistant
- Manufactured with Microstop™ - anti-microbial rubber compound that inhibits growth of bacteria and fungi

Description

Multi-Mat II™ is a reversible drainage mat that offers anti-slip traction in wet or greasy areas. Made from general purpose (Black) and heavy-duty nitrile (Red) rubber compounds for varying degrees of grease and oil protection, Multi-Mat II™ is available in sheet sizes or rolls for longer length application requirements. Its reversible construction design adds to the service life of the mat and a drainage system removes liquids from the work area. A low profile allows for easy cart access.

Specifications

Model No	T23S0032RD
Color	Red
Dimensions	2ft x 3ft
Thickness	3/8in
UPC	662641800960
Brand	NoTrax
Special Price Type	Sale
Available Colors	Red
Roll Sizes	2'x30', 2'x32', 2'x60', 3'x32', 3'x64', 4'x30', 4'x32', 4'x64'
Standard sizes	2'x3', 2'x8', 3'x4', 3'x8', 4'x8'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Greasy Areas
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Exceptional non-slip properties in a reversible mat - double the service life.
Edges	No borders
Usage Intensity	Medium duty
Material Specifications	75% Nitrile rubber
Surface Detail	Perforated Drainage Pattern
Process	Compression Molding
Pallet Quantity	60
Weight Lbs/sqft	1.2
Thickness Inch	3/8in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).

Slip Resistance Rating	Superior
Comfort Rating	Good
Grease Resistance Rating	Superior
Wearability Rating	Better