



BARREL EQUIPMENT

For easy and efficient dispensing of oils and fluids from barrels.

PART # 950000

LEVER ACTION BARREL PUMP

Ideal for oil and oil based fluids.

DELIVERS

1 liter / 12 strokes

Designed to fit containers ranging in size from 15 gallon (50 liters) through to 55 gallon (205 liters), this popular lever action pump is engineered for professional use. Ideal for oil and oil based fluids the pump has:

- A plated steel lever handle with rubber grip for convenience
- Built in 1.5" and 2" bung for use on drums with either opening
- Premium powder coated steel pump body with ribbed section aluminum die cast pump head for maximum strength
- Curved metal spout and telescopic suction tube

With a non return **Viton®** seal the pump can also be used with antifreeze, solvents, thinners, automotive additives, industrial chemicals and other non corrosive liquids. It is not suitable for water based fluids, gasoline and corrosive media.



PART # 950020

ROTARY BARREL PUMP

Ideal for use in industrial & automotive applications.

DELIVERS

1 liter / 12 strokes

This heavy duty rotary barrel pump has an aluminum die cast body and includes a 2" cast iron bung adaptor and die cast aluminum handle with security locking latch.

- Complete with a 3 pc threaded suction tube for use on 15 gallons (50 liter) – 55 gallons (205 liter) barrels
- Recommended for use with lubricating oils up to SAE 30, gasoline, diesel fuel and kerosene.
- Do not use – with corrosive liquids, solvents, acids, alkalis etc
- 1.8 m PVC nitrile delivery hose with metal nozzle, spring and hose clamp



WARNING!

Never operate the pump near fire or source of spark. Some media may be explosive and dangerous to pump.

PART # 950150

DRUM OPENER

An easy and convenient tool to open almost all types of drums.

- Ends of the wrench are designed to fit perfectly onto most 2" and ¾" Drum Plugs
- Compact design for easy storage, the opener is manufactured from cast aluminum, hardened and tempered for increased strength



SIGHT GLASSES AND FLUID ANALYSIS SYSTEMS



Viton® O-Ring only with BSPP & Metric size sight glasses.

Quick and easy condition assessment of your equipment's vital fluids to help insure cleanliness, reducing downtime and maintenance costs.

The easy-to-install and access fluid analysis system and sight glass gives you greater insight into the status of fluids and helps your respond before major issues arise.

- Flat front sight glass with etched and painted crosshairs, allowing a clear view of fluids without distortion
- Recommended Temperature: -40°F to 200°F (-40°C to 93°C)
- UV-resistant to protect against long-term sun exposure
- Shatterproof, stain-proof and chemically resistant
- Fluid Analysis System
 - Dimensions - 2.75" x 3.18" x 3.5" (w x h x l)
- Large Tritan™ sight glass with 1.4" diameter x 1.25" deep viewing area
- Aluminum body
- Steel Adapter
- Standard flow sampling valve with stainless steel pilot tube
- Magnetic plug
- M16 x 2 sample port threads for attaching to vacuum pump and sample bottle
- Steel corrosion indicator
- Viton® o-ring

DESCRIPTION	THREAD SIZES	PART #	S	D	L	V
Sight Glass	1" NPT MALE	466520	1 1/16"	1.18	1.10	.248 fl. oz.
Sight Glass	¾" NPT MALE	466515	1 1/8"	1.00	1.10	.148 fl. oz.
Sight Glass	½" NPT MALE	466505	7/8"	.78	.98	.063 fl. oz.
Sight Glass	¾" NPT MALE	466510	¾"	.63	.98	.054 fl. oz.
Sight Glass	¼" NPT MALE	466500	5/8"	.46	.73	.022 fl. oz.
Sight Glass	1" BSPP MALE	466590	1 1/16"	1.18	1.10	.248 fl. oz.
Sight Glass	¾" BSPP MALE	466560	1 1/8"	1.00	1.10	.148 fl. oz.
Sight Glass	½" BSPP MALE	466565	7/8"	.78	.98	.063 fl. oz.
Sight Glass	¾" BSPP MALE	466555	¾"	.63	.98	.054 fl. oz.
Sight Glass	¼" BSPP MALE	466550	5/8"	.46	.73	.022 fl. oz.
Sight Glass	M10 x 1" THREADS	466545	7/16"	.32	.59	.004 fl. oz.
Sight Glass	M12 x 1.5" THREADS	466540	7/16"	.32	.59	.004 fl. oz.
Sight Glass	M20 x 1.5" THREADS	466535	7/8"	.78	.96	.061 fl. oz.
Sight Glass	M22 x 1.5" THREADS	466570	7/8"	.78	.96	.061 fl. oz.
Fluid Analysis System	1 1/2" NPT THREADS	830150				
Fluid Analysis System	1 1/4" NPT THREADS	830125				
Fluid Analysis System	1" NPT THREADS	830100				
Fluid Analysis System	¾" NPT THREADS	830075				
Fluid Analysis System	½" NPT THREADS	830050				
Fluid Analysis System	1" BSPP THREADS	830100B				
Fluid Analysis System	¾" BSPP THREADS	830075B				
Fluid Analysis System	½" BSPP THREADS	830050B				
Fluid Analysis System	M20 x 1.5" THREADS	830150M				

S - Wrench Size D - Diameter L - Length V - Volume