

Oil Safe Filter Cart



Stationary wall mount version



Oil Safe Filtration Units

These filtration units extend the life of your industrial oils, saving you time and money. They maintain purity from storage to application and eliminate cross-contamination with color-coded error-proof, flat face, zero leak Quick Connects.

Includes a 1200 RPM electric motor/pump to reduce oil shearing and electrostatic charges frequent in higher RPM motors. Filters that are beta 2000 (99.95% efficient) with medium pressure, compared to low pressure types which can flex, distort, and collapse. These filters have two seals which protect the filter ID and OD to reduce oil bypassing the filter element. They do not leak unfiltered oil across a bypass valve in the filter head; 100% of all oil passes through the filter media. All of these features equate to better particulate removal.

With three layers of spill containment, 24VDC controls, electrical overload protection, and zero-leak quick connects lead to safe operation.

Part #	Description
FF57700 Basic	Wall Mount Stationary Filtration Unit - Basic
FF57710 Pro	Wall Mount Stationary Filtration Unit - Pro
FF57780 Basic	Portable Filtration Cart - Basic
FF57790 Pro	Portable Filtration Cart - Pro

	Stationary		Portable	
	Basic	Pro	Basic	Pro
Customized color-coded identification	•	•	•	•
1HP fully enclosed fan cooled electric motor	•	•	•	•
Oil pump with integral relief valve	•	•	•	•
Upstream and downstream oil sample ports	•	•	•	•
Power coated finish on steel frame	•	•	•	•
1200 RPM electric motor	•	•	•	•
System operating pressure gauge	•	•	•	•
Full front panel for spill containment	•	•	•	•
Removable filter element spill containment	•	•	•	•
Lower frame spill containment	•	•	•	•
Medium pressure non-bypassing filters	•	•	•	•
Beta 2000 filters 99.95% efficient	•	•	•	•
ID and OD filter seals	•	•	•	•
Differential visual filter indicators	•	•	•	•
Differential electrical filter indicators & lights		•		•
24VDC controls		•		•
Convenient and secure transfer hose storage			•	•
15" Heavy duty pneumatic wheels			•	•
Isolation front feet			•	•
Retractable 40ft electric cord reel			•	•
8ft wire reinforced transfer hoses			•	•
Adjustable overload protection		•		•
Color-coded zero leak quick connects				•