




Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Nickel Finish

By RACO
Catalog # 6239NI



Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Nickel Finish

Features

- Can be used for power/data
- 15A, 125V tamper resistant receptacle
- Removable neoprene gaskets allow for independent use of either side of the receptacle with cover closed
- Recessed receptacle minimizes plug protrusion
- Height accessible adjustments after box is mounted

Application

Carpet;Tile;Wood

Specifications

Buy American Compliant Certified Listed	Contact Manufacturer • UL Listed • CSA Certified
Buy America(n) Qualified	Contact Manufacturer

Configuration

Number of Gang(s)	1-Gang
-------------------	--------

Dimensions

Package Height	5.938 in
Length	5.813 in
Package Weight	2.47 lb.
Cubic Capacity	28.0 cu.in
Package Length	5.813 in
Package Width	5.625 in

Weight	2.47 lb.
Height	5.938 in
Width	5.625 in
Size	1-Gang
Dimensions	5.813 in x 5.625 in x 5.938 in

General

Color	Nickel
Product Family	Wood Floor Boxes
Cover Shape	Round
Type of Use	Wood
Product Type	Floor Boxes
UPC	050169947142
Type	• Boxes • Covers
Material	Steel
Cover Type	Round

Logistics

Minimum Pack Quantity	1
Pallet Quantity	245
Carton Quantity	1

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)