

## Premium Duty Spring Retractable Reels

**Air/Water/Oil/Grease** - 1/4", 3/8", 1/2" I.D.

- Compact for a wide range of applications with critical space requirements
- Robotically welded steel base offers maximum strength and consistent quality
- Individually powder-coated steel components provide maximum protection from premature corrosion
- Guide arm adjusts to two positions
- Inlet hose is plumbed into the base to eliminate the risk of stress on the swivel
- The reliable speed latch allows for positive locking of the spool in two positions per rotation
- The swivel is nested inside the spool for protection from impact and the environment



5635 OLP



5650 OLP



### Additional Series 5000 / 5005 Models

**Enclosed Reels** - Page 10

**Pre-Rinse** - Page 19

**Gas Welding** - Pages 32-33


**Twin Hydraulic** - Page 18

**Cord Reels** - Page 26-29

Model with hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		Max Pressure		NPT(M) Hose Outlet	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index #
	lbs	kg	in	mm	in	mm	ft	m	psi	bar	in	in	in	
<b>Low Pressure Air/Water Reels</b> Maximum Temperature 150°F (65°C) Max working pressure is at 70°F (20°C)														
5450 OLP	26	12	1/4	6	.475	12	50	15	300	21	1/4	3/8	1/4	1
5635 OLP	25	11	3/8	10	.600	15	35	11	300	21	1/4	3/8	1/4	1
5650 OLP	36	16	3/8	10	.600	15	50	15	300	21	1/4	3/8	1/4	2
A5825 OLP	27	12	1/2	13	.750	19	25	8	300	21	1/2	3/8	1/2	1
A5835 OLP	39	18	1/2	13	.750	19	35	11	300	21	3/8	3/8	1/2	2
A5850 OLP	41	19	1/2	13	.750	19	50	15	300	21	1/2	3/8	1/2	3
<b>Medium Pressure Oil Reels</b> Maximum Temperature 210°F (99°C)														
5630 OMP	31	14	3/8	10	.690	18	30	9	2600	179	3/8	3/8	3/8	1
A5835 OMP	42	19	1/2	13	.820	21	35	11	3000	207	1/2	3/8	1/2	2

Low pressure reels supplied with PVC hose. Medium pressure reels supplied with S.A.E. 100R1-AT (3/8") or S.A.E. 100R17 (1/2") one wire braid hose.

	Dimensions					
	1		2		3	
	in	mm	in	mm	in	mm
<b>A</b>	14 <sup>3/8</sup>	365	17 <sup>5/8</sup>	448	17 <sup>5/8</sup>	448
<b>B</b>	13 <sup>3/4</sup>	349	16 <sup>3/4</sup>	425	16 <sup>3/4</sup>	425
<b>C</b>	9 <sup>3/4</sup>	248	9 <sup>3/4</sup>	248	9 <sup>3/4</sup>	248
<b>D</b>	2 <sup>1/2</sup>	64	2 <sup>1/2</sup>	64	2 <sup>1/2</sup>	64
<b>E</b>	6 <sup>1/8</sup>	156	5 <sup>7/8</sup>	149	7 <sup>1/4</sup>	184



Model without hose & bumper	Shipping Weight		Hose Capacity				Max Pressure		NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index #		
	lbs	kg	I.D.		O.D.		Length		in	in			
<b>Low Pressure Air/Water Reels</b> Maximum Temperature 210°F (99°C)													
5400 OLP	20	9	1/4	6	.475	12	50	15	500	35	3/8	1/4	1
5600 OLP	21	10	3/8	10	.600	15	35	11	500	35	3/8	1/4	1
5605 OLP	21	10	3/8	10	.600	15	50	15	500	35	3/8	1/4	2
A5800 OLP	22	10	1/2	13	.750	19	25	8	500	35	3/8	1/2	1
A5806 OLP	35	16	1/2	13	.750	19	50	15	500	35	3/8	1/2	3
<b>Medium Pressure Oil Reels</b> Maximum Temperature 210°F (99°C)													
5400 OMP	23	10	1/4	6	.530	13	35	11	3000	207	3/8	3/8	1
5600 OMP	24	11	3/8	10	.690	18	30	9	3000	207	3/8	3/8	1
<b>High Pressure Grease Reels</b> Maximum Temperature 210°F (99°C)													
5400 OHP	23	10	1/4	6	.580	15	30	9	5000	345	1/4	1/4	1



### Interactive Reel Catalog

Visit [reelcraft.com/catalog](http://reelcraft.com/catalog) for complete product specifications, available parts, and accessories.



**Pivot Bases & Swing Brackets**  
See page 39