


**E A 3 3 1 06 L 12D**

<b>Drive Type</b>	<b>Swivel Size</b>	<b>Width of Spool</b>	<b>Motor Voltage/H.P.</b>
A - Air motor B - Bevel crank C - Hand crank E - Electric motor	2 - 1/2" (13 mm) I.D. 3 - 3/4" (19 mm) I.D. 6 - 1/4" (6 mm) Dual 7 - 1" (25 mm) I.D. 8 - 1/2" (13 mm) I.D. pressure wash	See "F" Dimension 06 - 6" (152 mm) 12 - 12" (305 mm) 18 - 18" (457 mm) 22 - 22" (559 mm) 28 - 27" (711 mm)	Blank - No Motor 12D - 12 V DC 4A - 1/2 HP air motor
<b>Fluid Path Type</b>	<b>Pressure</b>		
A - Gooseneck H - Heavy duty gooseneck (1" only)	L - 1000 PSI (69 bar) M - 3000 PSI (207 bar)		

**NOTE:** Chart is for reference only. Not all options available in every combination. Reels cannot be ordered by selecting from this chart.

Hose I.D.	1/4"	3/8"	1/2"	3/4"	1"
	6 mm	10 mm	13 mm	19 mm	25 mm
Hose O.D.	.530"	.710"	.850"	1.188"	1.375"
	13 mm	18 mm	22 mm	30 mm	35 mm
"F" Width	Hose Capacity				
6"	200'	140'	100'	50'	N/A
152 mm	61 m	43 m	30 m	15 m	
12"	425'	300'	200'	100'	50'
305 mm	130 m	91 m	61 m	30 m	15 m
18"	625'	450'	325'	175'	100'
457 mm	191 m	137 m	99 m	54 m	31 m
22"	780'	550'	400'	225'	125'
559 mm	238 m	168 m	122 m	69 m	38 m
27"	1000'	700'	500'	275'	150'
686 mm	305 m	213 m	152 m	84 m	46 m



**Additional Series 30000 Models**

<b>Pressure Wash -</b> Page 20	<b>Hose Reel Cart -</b> Page 21	<b>Gas/Cable Welding -</b> Pages 32-34
-----------------------------------	------------------------------------	---

Model without hose & bumper	Shipping Weight		Hose Capacity				Max Pressure	NPT(F) Reel Inlet	NPT(F) Reel Outlet	D		E		F		G				
	lbs	kg	I.D.	O.D.	Length	in				mm	in	mm	in	mm	in	mm	in	mm		
<b>Manual Hand Crank Hose Reels</b> Maximum Temperature 210°F (99°C)																				
CA32106 L	40	18	1/2	13	.750	19	100	30	100	69	1/2	1/2	9 <sup>3</sup> / <sub>4</sub>	248	19 <sup>3</sup> / <sub>4</sub>	502	6	152	6 <sup>3</sup> / <sub>8</sub>	162
CA32112 L	46	21	1/2	13	.750	19	200	61	1000	69	1/2	1/2	15 <sup>3</sup> / <sub>4</sub>	400	25 <sup>3</sup> / <sub>4</sub>	654	12	305	6 <sup>3</sup> / <sub>8</sub>	162
CA32118 L	51	23	1/2	13	.750	19	325	99	1000	69	1/2	1/2	21 <sup>3</sup> / <sub>4</sub>	552	31 <sup>3</sup> / <sub>4</sub>	806	18	457	6 <sup>3</sup> / <sub>8</sub>	162
CA32106 M	42	19	1/2	13	.850	22	100	30	3000	207	1/2	1/2	9 <sup>3</sup> / <sub>4</sub>	248	19 <sup>3</sup> / <sub>4</sub>	502	6	152	6 <sup>3</sup> / <sub>8</sub>	162
CA32112 M	46	21	1/2	13	.850	22	200	61	3000	207	1/2	1/2	15 <sup>3</sup> / <sub>4</sub>	400	25 <sup>3</sup> / <sub>4</sub>	654	12	305	6 <sup>3</sup> / <sub>8</sub>	162
CA32118 M	52	24	1/2	13	.850	22	325	99	3000	207	1/2	1/2	21 <sup>3</sup> / <sub>4</sub>	552	31 <sup>3</sup> / <sub>4</sub>	806	18	457	6 <sup>3</sup> / <sub>8</sub>	162
CA33106 L	41	19	3/4	19	1.075	27	50	15	1000	69	3/4	3/4	9 <sup>3</sup> / <sub>4</sub>	248	19 <sup>3</sup> / <sub>4</sub>	502	6	152	6 <sup>3</sup> / <sub>8</sub>	162
CA33112 L	46	21	3/4	19	1.075	27	100	30	1000	69	3/4	3/4	15 <sup>3</sup> / <sub>4</sub>	400	25 <sup>3</sup> / <sub>4</sub>	654	12	305	6 <sup>3</sup> / <sub>8</sub>	162
CA33118 L	51	23	3/4	19	1.075	27	175	53	1000	69	3/4	3/4	21 <sup>3</sup> / <sub>4</sub>	552	31 <sup>3</sup> / <sub>4</sub>	806	18	457	6 <sup>3</sup> / <sub>8</sub>	162
CA33112 M	47	21	3/4	19	1.188	30	100	30	3000	207	3/4	3/4	15 <sup>3</sup> / <sub>4</sub>	400	25 <sup>3</sup> / <sub>4</sub>	654	12	305	6 <sup>3</sup> / <sub>8</sub>	162
CA33118 M	51	23	3/4	19	1.188	30	175	53	3000	207	3/4	3/4	21 <sup>3</sup> / <sub>4</sub>	552	31 <sup>3</sup> / <sub>4</sub>	806	18	457	6 <sup>3</sup> / <sub>8</sub>	162
CH37112 L*	60	27	1	25	1.375	35	50	15	1000	69	1	1	15 <sup>3</sup> / <sub>4</sub>	400	25 <sup>3</sup> / <sub>4</sub>	654	12	305	8	203
CH37118 L*	64	29	1	25	1.375	35	100	30	1000	69	1	1	21 <sup>3</sup> / <sub>4</sub>	552	31 <sup>3</sup> / <sub>4</sub>	806	18	457	8	203
<b>Electric Motor Driven Hose Reels</b> Maximum Temperature 210°F (99°C). Motor control accessories not included.																				
EA32106 L12D	60	27	1/2	13	.750	19	100	30	1000	69	1/2	1/2	9 <sup>3</sup> / <sub>4</sub>	248	19 <sup>5</sup> / <sub>8</sub>	498	6	152	6 <sup>3</sup> / <sub>8</sub>	162
EA32112 L12D	64	29	1/2	13	.750	19	200	61	1000	69	1/2	1/2	15 <sup>3</sup> / <sub>4</sub>	400	23 <sup>7</sup> / <sub>8</sub>	606	12	305	6 <sup>3</sup> / <sub>8</sub>	162
EA32118 L12D	68	31	1/2	13	.750	19	325	99	1000	69	1/2	1/2	21 <sup>3</sup> / <sub>4</sub>	552	29 <sup>5</sup> / <sub>8</sub>	752	18	457	6 <sup>3</sup> / <sub>8</sub>	162
EA33106 L12D	63	29	3/4	19	1.075	27	50	15	1000	69	3/4	3/4	9 <sup>3</sup> / <sub>4</sub>	248	19 <sup>5</sup> / <sub>8</sub>	498	6	152	6 <sup>3</sup> / <sub>8</sub>	162
EA33112 L12D	68	31	3/4	19	1.075	27	100	30	1000	69	3/4	3/4	15 <sup>3</sup> / <sub>4</sub>	400	23 <sup>7</sup> / <sub>8</sub>	606	12	305	6 <sup>3</sup> / <sub>8</sub>	162
EA33118 L12D	68	31	3/4	19	1.075	27	175	53	1000	69	3/4	3/4	21 <sup>3</sup> / <sub>4</sub>	552	29 <sup>5</sup> / <sub>8</sub>	752	18	457	6 <sup>3</sup> / <sub>8</sub>	162
EH37118 L12D*	82	37	1	25	1.375	35	100	30	1000	69	1	1	21 <sup>3</sup> / <sub>4</sub>	552	31	787	18	457	8	203
<b>Air Motor Driven Hose Reels</b> Filter, regulator, lubricator required. Maximum Temperature 210°F (99°C). Motor control accessories not included.																				
AA32106 L4A	54	24	1/2	13	.750	19	100	30	1000	69	1/2	1/2	9 <sup>3</sup> / <sub>4</sub>	248	17 <sup>1</sup> / <sub>4</sub>	438	6	152	6 <sup>3</sup> / <sub>8</sub>	162

**CAUTION:** To prevent drum damage fully extend and pressurize hose and rewind on the reel. \*All 1 in. reel models have an 8 in. (203 mm) diameter carbon steel drum.

Many more reel models available in addition to chart. Refer to reelcraft.com for details.