

Third Party Listings



UL 355 - UL Standard for Safety Cord Reels

UL Listing means that **UL** has tested representative samples of a product and determined that the product meets specific, defined requirements. These requirements are often based on **UL's** published and nationally recognized Standards for Safety.

- UL tests the product and the manufacturing facility to certify that the product is safe if used as intended
- Recognized as the standard worldwide
- Mitigates insurance liability



CSA - C22.2 NO. 21-95 - Cord Sets & Power Supply Cords

CSA International certification marks indicate that a product, process or service has been tested to a Canadian or U.S. standard and it meets the requirements of an applicable **CSA** standard or another recognized document used as a basis for certification.

- Similar to UL, but preferred in some instances



L 4545 123 7

Triple Tap Power Cord Reels



- A heavy duty collector ring assures highest conductivity
- The reliable speed latch allows for positive locking of the spool in two positions per rotation
- Individually powder-coated steel components provide maximum protection from premature corrosion
- Robotically welded steel base offers maximum strength and consistent quality




L 4545 123 9G

Model w/ cord & bumper	Cord Ending	Cord Specifications				Volts	Amps	Shipping Weight		Size Index #
		AWG	mm ²	# Cond	ft m			Type**	lbs	
L 4050 163 9	Triple tap outlet NEMA 5-15R, Inlet straight blade plug NEMA 5-15P	16	1.33	3	50 15	SJE00W	125	13	26 12	1
L 4545 123 9		12	3.32	3	45 14	SJE00W	125	15	28 13	1
L 70075 123 9		12	3.32	3	75 23	SE00W	125	15	71 32	5
L 70100 123 9		12	3.32	3	100 30	SE00W	125	15	75 34	5
L 4545 123 9G	Triple tap outlet w/ GFCI* NEMA 5-15R, Inlet straight blade plug NEMA 5-15P	12	3.32	3	45 14	SJE00W	125	15	29 13	1
L 70100 123 9G		12	3.32	3	100 30	SE00W	125	15	76 34	5
L 4545 123 9GC	Triple tap outlet w/ GFCI* NEMA 5-15R Inlet twist lock plug NEMA L5-15P	12	3.32	3	45 14	SJE00W	125	15	29 13	1

For indoor non-weathertight applications only. All models UL listed at 125 Volt 60 HZ single phase. Swing brackets or pivot bases should be used if cords are pulled at more than 45°, see page 39. *The GFCI Receptacle is designed to protect from line-to-ground shock hazards. It does not protect against short circuits or overloads; this is the function of the fuse or circuit breaker. **Cord type designation shows all combinations of cord types that may be used, only UL approved cord types will be used.

Cord End Specifications



Refer to page 30 for dimensional drawings.

Interactive Reel Catalog



Visit reelcraft.com/catalog for complete product specifications, parts, and accessories.