

Medium Duty Spring Retractable Reels



Air/Water - 1/4", 3/8", 1/2" I.D.

- Spool is constructed from a rugged engineered plastic
- The steel guide arm and base are stamped with ribs and gussets to ensure maximum strength and lightest possible weight
- Guide arm adjusts to seven positions
- Widened ratchet and latch pawl design greatly reduces wear and increases service life
- The industrial-grade drive spring completely containerized and permanently sealed




RT650-OLP

Model with hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		Max Pressure		NPT(M) Hose Outlet	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index #
	lbs	kg	in	mm	in	mm	ft	m	psi	bar	in	in	in	
Low Pressure Air/Water Reels Maximum Temperature 150°F (65°C) Max working pressure is at 70°F (20°C)														
RT435-OLP	20	9	1/4	6	.475	12	35	11	300	21	1/4	3/8	1/4	1
RT450-OLP	24	11	1/4	6	.475	12	50	15	300	21	1/4	1/2	1/4	1
RT650-OLP	27	12	3/8	10	.600	15	50	15	300	21	1/4	1/2	1/4	1
RT835-OLP	27	12	1/2	13	.750	19	35	11	300	21	1/2	1/2	1/2	1
RT850-OLP	37	17	1/2	13	.750	19	50	15	300	21	1/2	1/2	1/2	2

Reels supplied with PVC hose.

Model without hose & bumper	Shipping Weight		Hose Capacity			Max Pressure	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index #				
	lbs	kg	I.D.	O.D.	Length								
Low Pressure Air/Water Reels Maximum Temperature 210°F (99°C)													
RT405-OLP	21	10	1/4	6	.475	12	50	15	300	21	1/2	1/4	1
RT605-OLP	22	10	3/8	10	.600	15	50	15	300	21	1/2	1/4	1
RT802-OLP	27	12	1/2	13	.750	19	35	11	300	21	1/2	1/2	1
RT805-OLP	25	11	1/2	13	.750	19	50	15	300	21	1/2	1/2	2

	Dimensions			
	1		2	
	in	mm	in	mm
A	17 ⁷ / ₈	454	17 ⁷ / ₈	454
B	16 ¹ / ₂	419	16 ¹ / ₂	419
C	6	152	6	152
D	2 ¹ / ₄	57	2 ¹ / ₄	57
E	6 ¹ / ₄	159	7 ³ / ₄	197



Premium Duty Spring Retractable Reels



Series 4000 - Air/Water - 1/4", 3/8" I.D.

- Compact for a wide range of applications with critical space requirements
- Inlet hose is plumbed into the base to eliminate the risk of stress on the swivel
- Guide arm adjusts to two positions
- The reliable speed latch allows for positive locking of the spool in two positions per rotation



4625 OLP

Series 4000 reels include a speed latch mechanism that uses a cam and disc for quiet operation.

Model with hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		*Max Pressure	NPT(M) Hose Outlet	NPT(F) Reel Inlet	NPT(F) Reel Outlet	
	lbs	kg	in	mm	in	mm	ft	m	psi	bar	in	in	
Low Pressure Air/Water Reels Maximum Temperature 150°F (65°C)													
4435 OLP	19	9	1/4	6	.475	12	35	11	300	21	1/4	3/8	1/4
4625 OLP	20	9	3/8	10	.600	15	25	8	300	21	1/4	3/8	1/4

Low pressure reels supplied with PVC hose. *Maximum working pressure at 70°F (20°C)

Model without hose & bumper	Shipping Weight		Hose Capacity			Max Pressure	NPT(F) Reel Inlet	NPT(F) Reel Outlet				
	lbs	kg	I.D.	O.D.	Length							
Low Pressure Air/Water Reels Maximum Temperature 210°F (99°C)												
4400 OLP	17	8	1/4	6	.475	12	35	11	500	35	3/8	1/4
4600 OLP	17	8	3/8	10	.600	15	25	8	500	35	3/8	1/4

	Dimensions	
	in	mm
	A	12 ⁷ / ₈
B	12 ⁵ / ₈	321
C	8	203
D	2 ¹ / ₂	64
E	5 ⁵ / ₈	143

Additional Series 4000 Models

Cord Reels - Page 27-30