





Blades not shown for clarity

CLOCKWISE
ROTATION



Ø 10.18 REF.

PD706273



03-56233 11-11 DD .62 CLW CC MP-C
12-Jul-13 14:45:57 #44 #990 01A



0832608371213M28

LABEL FORMAT

NOTES:

1. ALL DIMENSIONS IN INCHES
2. NO KEYWAY
3. FINISH: GALVANIZED
4. MATERIAL: STEEL
5. TOLERANCE (2PL.): $\pm .060$
6. AVG WT. (CALCULATED) W/.62 DIA HUB BORE. VARIATION CAN BE $\pm 11\%$
7. PD 706273 IS USED ON BLOWER HOUSING 70-106697-02

RHEEM P/N	MORRISON P/N	O.D. (IN.)	WIDTH (IN.)	NOMINAL SIZE	NO. BLADES	SET BACK (IN.)	HUB BORE DIA. (IN.)	ROTATION (HUB SIDE)	DISC SHAPE (HUB SIDE)	NO. OF SET SCREWS	WEIGHT (LBS.) SEE NOTE 6
PD706273	03-56233 (A)	11.93	11.93	11 X 11	54	5.97	0.62	CW	CONCAVE	2	7.3

CONFIDENTIAL

THIS PRINT, AND THE SPECIFICATIONS CONTAINED IN IT, IS THE PROPERTY OF RHEEM MANUFACTURING AND HAS BEEN ISSUED WITH THE UNDERSTANDING THAT IT WILL NOT BE REPRODUCED, REVEALED TO, OR USED FOR THE MANUFACTURE FOR OTHERS, AND WILL BE RETURNED UPON REQUEST.

STANDARD TOLERANCE UNLESS OTHERWISE SPECIFIED

FRACTIONAL: $\pm 1/32$
ANGULAR: $\pm 2^\circ$
DECIMAL: 2 PL = $\pm .030$
3 PL = $\pm .010$
DIMENSIONS IN () REF. ONLY

REVISIONS

NO REVISION TO DESIGN, MATERIAL, TOOLING, OR PROCESS IS ACCEPTABLE WITHOUT PRIOR APPROVAL FROM RHEEM THROUGH A REVISED ENGINEERING SPECIFICATION AND A RESAMPLING OF PARTS. THE SUPPLIER IS RESPONSIBLE FOR NOTIFYING RHEEM PARTS DIVISION IN WRITING OF ANY CHANGES AFFECTING PRODUCT QUALITY, PERFORMANCE, RELIABILITY, PACKAGING, DELIVERY, OR WORKMANSHIP. ANY DOCUMENTS REFERRED TO ON THIS DRAWING ARE INCLUDED IN THE SPECIFICATIONS FOR THIS COMPONENT.

ALL DIMENSIONS ARE IN INCHES
UNLESS OTHERWISE SPECIFIED



Replacement
Parts
Division

MODELED BY: JNF
APPROVED BY: ESP

DATE: 09-29-2020
DATE: 01-18-2021

ALL BENDS ARE 90° UNLESS
OTHERWISE SPECIFIED

BLOWER WHEEL
11 11 DD 0.62 CLW CC WHL

PART NO. SHEET 1 OF 1
PD706273

REV.
-