

## STARPOINT VRS-0,3t-M8

Artikel-Nr: 7100554




- Lifting points pivots 360°. Easy adjustment in load direction.
- ICE-Bolt made out of patented steel. Non-hazardous deep temperature usage down to -60°; higher toughness and therefore higher bending strength as well as less wear occurrence.
- Not exchangeable ICE-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no, ICE.
- Variable bolt lengths available for tapped or through holes.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread 8UN (ANSI B1.1) - Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Tested and certified by DGUV. Testing specifications: GS-HM-36: 2023-06, Certificate No.: HM 250037
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts (Version VRS-F).
- For permanent installation and recurrent lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## STARPOINT VRS-0,3t-M8

Artikel-Nr: 7100554



<b>weight</b>	0.11 kg	0.24 lbs
<b>Nominal WLL</b>	300 kg	660 lbs
<b>T</b>	35 mm	1-3/8"
<b>B</b>	11 mm	7/16"
<b>C</b>	9 mm	11/32"
<b>D</b>	25 mm	63/64"
<b>E</b>	25 mm	63/64"
<b>G</b>	30 mm	1-3/16"
<b>I</b>	16,3 mm	41/64"
<b>K</b>	47 mm	1-7/8"
<b>L</b>	12 mm	15/32"
<b>M</b>	M8 mm	M8
<b>N</b>	6 mm	15/64"