

## Load ring VLBG-Z 1,5t 5/8"-18UNF with RUD-bolt

Artikel-Nr: 7903942




- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Captive but exchangeable RUD-Bolt** with special corrosion protection Corrod-DT. Original RUD-Bolt is available as a spare part. Clear marking at the bolt head: RUD, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectively flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as:
  - Standard Metric Thread (DIN EN 13)
  - Metric Fine Thread (DIN EN 13)
  - Coarse Pitch Thread UNC (ANSI B1.1)
  - Fine Thread UNF (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- Component according to the test criterias of DGUV "GS-HM-36".
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift. Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## Load ring VLBG-Z 1,5t 5/8"-18UNF with RUD-bolt

Artikel-Nr: 7903942



<b>weight</b>	0.57 kg	1.26 lbs
<b>Nominal WLL</b>	1500 kg	3300 lbs
<b>T</b>	85 mm	3-11/32"
<b>A</b>	33 mm	1-5/16"
<b>B</b>	56 mm	2-3/16"
<b>C</b>	36 mm	1-27/64"
<b>D</b>	46 mm	1-13/16"
<b>E</b>	38 mm	1-1/2"
<b>F</b>	13,5 mm	17/32"
<b>G</b>	36 mm	1-27/64"
<b>H</b>	30 mm	1-3/16"
<b>I</b>	87 mm	3-7/16"
<b>K</b>	47 mm	1-7/8"
<b>L</b>	60 mm	2-3/8"
<b>M</b>	5/8"-18UNF mm	5/8"-18UNF
<b>N</b>	38 mm	1-1/2"