

Load ring, for welding VRBS-FIX - 100t

Artikel-Nr: 7906273




The VRBS-FIX with considerable improvements !

- Split force introduction due to multiple point fixing.
- Suspension ring pivots 180°.
- 100% WLL at 90° in the load ring plane possible.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). Weld: HY 28
- Clamping spring works as a noise reduction and holds the Oktagon-suspension ring in the requested position; therefore simple hinge of lifting mean possible.
- Patented markings for easy determination for withdraw of service. Patented markings for determination of the load angle.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- Clear marking of the minimum WLL for all loading directions.
- The weld-on-block is made (forged) out of a quality weldable steel.
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2021-09, Certificate-No.: HM 220056
- Significant product characteristics of the VRBS-FIX and VRBK-FIX are subject to property right claims.
- Simple and fast welding installation. Confirmation of the low temperature ability to -40°C by the notch bar impact test is possible upon request (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring, for welding VRBS-FIX - 100t

Artikel-Nr: 7906273



weight	148.20 kg	326.73 lbs
Nominal WLL	100000 kg	220460 lbs
T	390 mm	15-3/8"
A	320 mm	12-19/32"
B	97 mm	3-13/16"
C	195 mm	7-11/16"
D	250 mm	9-13/16"
E	763 mm	30"
F	392 mm	15-7/16"