

Lashing Point Welding LPW-U 32000 daN with spring

Artikel-Nr: 7906781




Original VIP-Quality

- Clear marking of the lashing capacity for all loading directions. LC marking with daN.
- Suspension ring pivots 180°.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- The weld-on-block is made (forged) out of quality weldable steel.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Phosphated surface.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW-U 32000 daN with spring

Artikel-Nr: 7906781



weight	7.12 kg	15.70 lbs
T	176 mm	6-15/16"
A	96 mm	3-25/32"
B	192 mm	7-9/16"
C	70 mm	2-3/4"
D	100 mm	3-15/16"
E	106 mm	4-3/16"
F	40 mm	1-9/16"
G	90 mm	3-17/32"
H	26 mm	1"
Lashing capacity	32000 daN	null