

Load ring VWBM 0,6t-M12

Artikel-Nr: 7909682




The first and currently only lifting point from RUD which provides an internal thread to be used for rotating and turning even under load.

- Ball bearing for a shock-free rotating and turning with less friction.
- Lifting points pivots 360°.
- Suspension ring with enlarged pivoting area.
- Patented markings for easy determination for withdraw of service as well as the determination of the load angle.
- Rotatable at nominal WLL, 90° to the bolt-on direction.
- Large distance between bolt-on surface and load to avoid damage.
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.
- Minimum grade 10.9
- min. thread engagement length 1,1 x M
- max. thread engagement length 1.6 x M

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VWBM 0,6t-M12

Artikel-Nr: 7909682



weight	0.61 kg	1.34 lbs
Nominal WLL	600 kg	1320 lbs
T	122 mm	4-13/16"
A	10 mm	3/8"
B	49 mm	1-15/16"
C	35 mm	1-3/8"
D	41 mm	1-5/8"
E	36 mm	1-27/64"
F	15 mm	19/32"
G	62 mm	2-7/16"
H	21 mm	13/16"
M	M12 mm	M12