

Load ring VWBM 1t-M16

Artikel-Nr: 7909683




The first and currently only lifting point from RUD which provides an internal thread to be used for rotating and turning even under load.

- Ball bearing for a shock-free rotating and turning with less friction.
- Lifting points pivots 360°.
- Suspension ring with enlarged pivoting area.
- Patented markings for easy determination for withdraw of service as well as the determination of the load angle.
- Rotatable at nominal WLL, 90° to the bolt-on direction.
- Large distance between bolt-on surface and load to avoid damage.
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.
- Minimum grade 10.9
- min. thread engagement length 1,1 x M
- max. thread engagement length 1.6 x M

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VWBM 1t-M16

Artikel-Nr: 7909683



weight	0.91 kg	2.01 lbs
Nominal WLL	1000 kg	2200 lbs
T	131 mm	5-3/16"
A	13 mm	1/2"
B	46 mm	1-13/16"
C	38 mm	1-1/2"
D	46 mm	1-13/16"
E	41 mm	1-5/8"
F	20 mm	3/4"
G	73 mm	2-7/8"
H	27 mm	1-1/16"
M	M16 mm	M16